

**Digital universal depth gauge, Measuring range: 600mm****Order data**

Order number	418770 600
GTIN	2050001670885
Item class	46P

Description**Version:**

Flexible universal depth gauges with exchangeable measuring tips. For measuring cut-outs, grooves, recesses, shoulders etc. Precision lapped measuring faces.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Depth gauge, double hook measuring tip No. 418772 size A, 1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498948.

Measuring tips No. 418772.

Measurement head No. 418774.

Technical description

Bridge length	150 mm
Measuring range	0 - 600 mm
Cross-section measuring beam	12x4 mm
Interface	USB interface
Interface	RS232 interface
Reversible reading	0.0005 in
Reversible reading	0.01 mm

Data sheet

Error limit	0.03 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
#Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/418770-600>