

**Value pack instant adhesive, 5 pieces****Order data**

Order number	GG3361 BLACK
GTIN	4069515051835
Item class	GGN

Description**Version:**

Universally applicable for bonding dissimilar materials. Hardens by atmospheric humidity. Black instant adhesive, very suitable for **bonding a wide range of materials** such as **metal to rubber** or **metal to plastic**.

Supplied with:

5 × instant adhesive, high viscosity, black, 20 g, No. 083361 BLACK.

Note:

Not available in all countries. Express delivery not available.

Technical description

Tensile shear strength	18 - 28 N/mm ²
Chemical basis	Ethyl cyanoacrylate
Operating temperature range	-55 - 95 °C
Density	1.06 g/cm ³
Touch dry after	30 - 90 s

Data sheet

Colour	black
Shape	liquid
Storage temperature	20 °C
Labelling of hazardous substances	GHS07 caution
Capacity	20 ml
Dynamic viscosity	2000 - 4000 mPas
Product name attribute	20 g
Type of product	Instant adhesive

Suitable products

No Shop URL available for: GG3361 BLACK