HOLEX

Boring bar for threading inserts, right-hand, Insert size L / type: 16/1mm

Order data

Order number	272185 16/1
GTIN	4069515112888
Item class	22B

Technical description

Inclination angle	1.5 degrees
Neck width L_4	15 mm
Overall length L	150 mm
Centre offset L_3	10.25 mm
Shank ⌀ D_S	16 mm
Through-coolant	no
Minimum pre-drill ⌀ D_{min}	20 mm
Version	Steel
Head length L_1	40 mm
Insert size	16 mm
Insert size L	16 mm

Application type	right-hand
Type of product	Boring bar