

**Value pack cup brush stainless steel wire 0.30 mm****Order data**

Order number	GG5732 80
GTIN	4067263136149
Item class	GGN

Description**Version:**

Waved wire firmly crimped into the steel body. For use on angle grinders and on stationary machines.

With **M14 internal thread**.

Corresponds to No. 573205. With **M14 internal thread**.

Application:

Very well suited for brushing surfaces, deburring, removing rust, polishing, removing paint, primer, varnish, scale etc.

Technical description

Thread M	M14
maximum speed	8500 min ⁻¹
Brush Ø D ₁	85 mm
Length of brush section H ₁	25 mm
Bristle thickness	0.3 mm

Contents	5
Brush material	Stainless steel wire
Twisted knotting	waved
Type of product	Cup brush

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG5732-80>