

Garant**Softcut® shoulder mill with plain shank, for indexable inserts AO..****Order data**

Order number	215407 25/4
GTIN	4069515038584
Item class	210

Description**Version:**

High precision square shoulder mill with irregular pitch for very smooth cutting, very high precision and cutting power. **With special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or for spindles with low drive power.

Application:

For shoulder milling in large depths, also slotting. General use in all steel materials as well as stainless and acid-resistant steels.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.5** with bit No. **674252 size 8IP**.

Technical description

Ramping length L for $\alpha_{\max}$	4.2 mm
Shank $\varnothing D_s$ h6	20 mm
suitable indexable insert	AO.T1104
$\varnothing D_3$	22 mm
Series	Softcut®
Circular interpolation milling a_p	4.8 mm
Circular interpolation milling $\varnothing D_{\min}$	38.9 mm
Cutting edge $\varnothing D_c$	25 mm
Overall length L_{tot}	180 mm
Set of insert screws	219799 10 (8IP; 1.5 Nm)

Data sheet

Overhang L_1	25 mm
Ramping angle $\alpha_{\max}$	4.1 degrees
Number of cutting edges Z	4
Circular interpolation milling $\varnothing D_{\max}$	47.3 mm
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Indexable end mill

Suitable products

No Shop URL available for: 215407 25/4