

Garant GRIDLINE

ESD tool cabinet complete with drawers 50 kg, 36x24G, Height mm / number of drawers: 800/6



Order data

Order number	972460 800/6
GTIN	4067263126539
Item class	9GK

Description

Version:

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Completely equipped tool cabinet in 40x28G, with drawers 36x24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25-mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Includes ESD grounding cable.

Colour:

Body and drawer body light grey similar to RAL 7035 **ESD powder-coated**.

Note:

- When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.
- All plastic components (e.g. covering caps and handles) are non-ESD conductive.

Technical description

Drawer usable area in G	36x24
Height	800 mm
Drawer usable width in G	36

Data sheet

Weight	138 kg
Usable height	700 mm
Drawer usable width	900 mm
Drawer usable depth	600 mm
Width	1000 mm
Drawer usable depth in G	24
Depth	700 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	36x24G
Type of product	Tool cabinet

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/972460-800/6>