

**Value pack LED headlamp with rechargeable battery****Order data**

Order number	GG1493 300
GTIN	4067263137955
Item class	GGN

Description**Version:**

LED work headlamp with wide spread of light for optimum illumination of the entire work area. Non-contact switching on and off, thanks to sensor system with 2 lighting levels.

Feature:

Contents: 4 pieces

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable.

Technical description

Illumination step 2	300 lm
Illumination time	6 h
Number of rechargeable batteries contained	4
Illumination	100 lm
Overall length	78 mm

Weight	111 g
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
ATEX zone	None
Illumination time stage 2	2 h
Overall width	47 mm
IP Index of Protection	IP 65
Type of product	Headband lamp

Accessories

LED headlamp with rechargeable battery Type 300	081493 300
---	------------