

Garant GRIDLINE

Computer terminal with printer flap, Type: FR



Order data

Order number	948112 FR
GTIN	4062406073756
Item class	9GS

Description

Version:

Monitor housing with fan for CRT monitors up to 19 inches. Swing door with polycarbonate window, lockable.

Keyboard drawer locks in full travel position. Three height adjustments at 60 mm intervals (1058 / 1118 / 1178 mm), can be locked, with palm rest of bamboo and cable strain relief.

Computer housing with fan and 1 height-adjustable galvanised shelf, and cable slots for a tidy cable layout. One key for all locks.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors and drawer front RAL 7016 anthracite **powder-coated**.

Note:

The dimensions of the computer workstation are compatible with GridLine cabinets depth 20G No. 940001 – 940217, 940801 – 940907 and can be combined with them as required.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Data sheet

Computer housing usable height	845 mm
Monitor housing usable width	690 mm
Computer housing usable depth	470 mm
Depth	500 mm
Monitor housing usable depth	458 mm
Dimensions printer flap	236×290 mm
Monitor housing usable height	570 mm
Weight	77 kg
Width	750 mm
Depth in G	20
Computer housing usable width	700 mm
Width in G	30
Viewing window height	532 mm
Height	2000 mm
maximum screen size, diagonal	19 in
Viewing window width	552 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
IP Index of Protection	IP 41
Power supply	Mains operated
On/Off switch	yes
Nominal voltage	250 V
#Plug type, input	E
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Computer workstation

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948112-FR>
