

Single test pin Tolerance class 2, Type: 11**Order data**

Order number	483910 11
GTIN	2050002076631
Item class	48A

Description**Version:**

Of high quality gauge steel, hardened (60 ± 2 HRC) and tempered. Surface ground and lapped. From $\varnothing$ 1.5 mm engraved with the size, 0.1 mm – 0.99 mm without a chamfer. From 1.0 mm one end chamfered.

Tolerance class 2: Pin $\varnothing \pm 0.002$ mm.

Application:

Degrease before use and grease after use.

Note:

When ordering, please additionally state the **desired $\varnothing$** , e.g. No. 483900 size 5 **10.08** or 483920 size 5 **10.082**.

Technical description

Pitch	0.01 mm
Nominal size	25 - 29.99 mm
Gauging pin length	70 mm
Calibration	L6
Standard	DIN 2269
Tolerance class	2
Hardness	60 ± 2 HRC
Material	Gauge steel
Type of product	Test pin

Services

CalibrationTest pin maximum Ø 20	028240 20
DAkkS calibrationTest pin maximum Ø 20	028260 20