

**Multimeter, Device type: 9917****Order data**

|              |               |
|--------------|---------------|
| Order number | 473320 9917   |
| GTIN         | 4045197554291 |
| Item class   | 42I           |

**Description****Version:**

Ergonomically shaped two-component casing with rubber cover. Large easy-to-read digital display with switchable background lighting. Auto ranging meters. All meters with test prod mounting on the rear for one-hand operation, with a stand.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

Digital service meters with comprehensive functions.

**Standard:**

**IEC / DIN EN 61010-1; GS T&Uuml;V Rheinland.**

**Supplied with:**

Supplied with batteries (2 pcs. size 960, 1 pc. size 9917), test prods No. 473328 size 2. Temperature sensor, cover caps, and carrying case.

**Technical description**

|           |                    |
|-----------|--------------------|
| Frequency | 0.001 Hz – 9.9 MHz |
|-----------|--------------------|

|                                                          |                              |
|----------------------------------------------------------|------------------------------|
| Information displayed                                    | 4000                         |
| Overvoltage category                                     | CAT IV 600 V; CAT III 1000 V |
| AC current                                               | 0,1 $\mu$ A – 10 A           |
| AC voltage                                               | 0.1 mV – 1000 V              |
| Basic accuracy                                           | 1.5 %                        |
| DC current                                               | 0,1 $\mu$ A – 10 A           |
| IP Index of Protection                                   | IP 67                        |
| Diode testing                                            | yes                          |
| Resistance                                               | 0.1 $\Omega$ – 40 M $\Omega$ |
| DC voltage                                               | 0.1 mV – 1000 V              |
| acoustic continuity test                                 | yes                          |
| Measurement process                                      | RMS                          |
| Manufacturer's designation                               | 9917                         |
| Data storage key                                         | yes                          |
| Display backlit                                          | yes                          |
| Temperature                                              | -20 - 760 °C                 |
| Capacitance                                              | 1 pF – 200 $\mu$ F           |
| automatic power-off                                      | yes                          |
| Calibration                                              | I3                           |
| #Number of batteries contained                           | 1                            |
| #Article no of the battery / rechargeable battery fitted | 081551 6LR61                 |
| Power supply                                             | Battery-powered              |
| Power supply                                             | No. 081556 size 6LR61        |
| Type of product                                          | Multimeter                   |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/473320-9917>