

Garant

Bi-hexagon socket, 1/4 inch deep, Width across flats: 10mm



Order data

Order number	631439 10
GTIN	4062406264383
Item class	61A

Description

Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads.

Close tolerance jaw sizes with **HT drive** profile protect corners of nuts and bolt heads. Thin walls for access to restricted places.

Square drive socket with hole to DIN 3120 D 6.3.

Standard:

DIN 3124-L

Material:

Chrome vanadium steel, chrome-plated.

Note:

GARANT and HOLEX bi-hex sockets, long also available in imperial sizes (GARANT: No. 631442; HOLEX: No. 631452).

Technical description

Width across flats	10 mm
Length	50 mm

Data sheet

Ø drive output end	14.5 mm
Square drive	1/4 in
Drive profile	Bi-hex socket
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Socket insert