

**Single test pin Tolerance class 2, Type: 4****Order data**

|              |               |
|--------------|---------------|
| Order number | 483910 4      |
| GTIN         | 2050001048936 |
| Item class   | 48A           |

**Description****Version:**

Of high quality gauge steel, hardened ( $60 \pm 2$  HRC) and tempered. Surface ground and lapped. From  $\varnothing$  1.5 mm engraved with the size, 0.1 mm – 0.99 mm without a chamfer. From 1.0 mm one end chamfered.

**Tolerance class 2:** Pin  $\varnothing \pm 0.002$  mm.

**Application:**

Degrease before use and grease after use.

**Note:**

When ordering, please additionally state the **desired  $\varnothing$** , e.g. No. 483900 size 5 **10.08** or 483920 size 5 **10.082**.

**Technical description**

|                    |                |
|--------------------|----------------|
| Gauging pin length | 70 mm          |
| Pitch              | 0.01 mm        |
| Nominal size       | 6 - 9.99 mm    |
| Calibration        | L5             |
| Standard           | DIN 2269       |
| Tolerance class    | 2              |
| Hardness           | $60 \pm 2$ HRC |
| Material           | Gauge steel    |
| Type of product    | Test pin       |

Services

|                                        |           |
|----------------------------------------|-----------|
| CalibrationTest pin maximum Ø 20       | 028240 20 |
| DAkkS calibrationTest pin maximum Ø 20 | 028260 20 |