

Rack panel for plain sheet metal doors, Type: S**Order data**

Order number	940705 S
GTIN	4062406068462
Item class	9GI

Description**Version:**

Of sheet metal for mounting hooks and open storage bins. The rack panels are screwed to the inside of swing doors, using the fastenings provided. **Only for cabinets with plain sheet metal swing doors of minimum size 750 mm wide and 1000 mm high.** Cabinets with a height of 2000 mm can take 2 panels per swing door. Load capacity per door: 10 kg. With slots to accept open storage bins No. 963321.

Colour:

RAL 7016 anthracite, **powder coated.**

Note:

- **Open storage bins and wide projecting tools cannot be inserted at the height of storage shelves.**
- **Suitable only for GridLine cabinets with swing doors.**

Technical description

Width	250 mm
Height	800 mm
Thickness	28 mm

Data sheet

Material thickness	0.9 mm
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Perforated rear panel