



Digital absolute dial indicator IP66, Measuring range: 5mm



Order data

Order number	434411 5
GTIN	4550501406635
Item class	40W

Description

Version:

Handy, versatile, and robust digital dial indicator with integral tolerance display (with or without measured value). The slim profile makes them particularly suitable for incorporation in jigs where space is restricted. The display can be turned through 180° to allow reading from both sides. **Short circuiting the Digimatic cable pins 1 and 6 allows one or a series of dial indicators to be set to zero or to a pre-selected value.** Reading from above.

Supplied with:

Including 1 battery No. 081560 357.

Optional extras:

Data cable No. 498428, special contact points No. 434900; 434910; 434915.

Technical description

Gauging force	2 N
Measurement variation E MPE (measurement range)	0.003 mm
IP Index of Protection	IP 66
Selectable display	0.01 / 0.001 mm

Data sheet

Clamping shank Ø h6	8 mm
Power supply	Battery-powered
#Article no of the battery / rechargeable battery fitted	081560 357
Measuring range	0 - 5 mm
#Number of batteries contained	1
Calibration	C1
Battery type	Button cell
Length	116.5 mm
Depth	44.3 mm
Width	35 mm
Standard	Works standard
Interface	USB interface
Interface	USB interface
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Type of product	Dial indicator