



Value pack thread locker, 5 pieces



Order data

Order number	GG3313 55-03
GTIN	
Item class	GGN

Description

Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic adhesives are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Application:

Low strength – can be undone with normal tools.

Medium strength – can still be undone with normal tools.

High strength – Can be undone only with special tools or by heating (>150 °C). Medium-strength, for use as screw locking and thread sealing up to 200 °C, also the passive materials, carries no hazard labels.

Supplied with:

5 × medium-strength thread locker, 50 ml, No. 083313 55-03.

Note:

Before applying locking fluid, clean the threads with general-purpose cleaner No. 083391 and No. 083392. Quick and easy handling for 50 ml bottles with No. 083344 size 50.

Technical description

Touch dry after	10 - 20 min
-----------------	-------------

Data sheet

Maximum gap size	0.25 mm
Colour	blue
Capacity	50 ml
Chemical basis	anaerobic methacrylate
Strength class	medium strength
Functional strength to	1 - 3 h
Suitable for application area	oily surfaces
Suitable for application area	Thread locker
Storage temperature	20 °C
Density	1.1 g/cm ³
Manufacturer's designation	55#-03
Working life after date of manufacture	12 mo
Flashpoint	100 °C
minimum break-away torque	18 - 23 Nm
Shape	liquid
Operating temperature range	-55 - 200 °C
Characteristics	vibration-resistant
Characteristics	thixotropic
Characteristics	labelling-free
Characteristics	Can be released with normal tools
Characteristics	sealing
for thread size M to	M36
Suitable for material	Metal
Dynamic viscosity	900 - 1500 mPas
Disassembly	with normal tool
Product name attribute	50 ml
Type of product	Thread locker

Suitable products

No Shop URL available for: GG3313 55-03

