

TRICOFLEX**AIRSOFT braided hose, black PVC, Length 50 m, Hose internal Ø: 13mm**

Order data

Order number	080037 13
GTIN	3506111000597
Item class	08A

Description

Version:

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.

Airsoft Performance braided hose, flexible oil-resistant compressed air hose for pneumatic tools.

Operating pressure 15 bar.

Technical description

maximum operating pressure	15 bar
Hose internal Ø	13 mm
Hose external Ø	20 mm
Product name attribute	Length 50 m
Type of product	Hose