

**PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 8m****Order data**

Order number	080248 8
GTIN	7391390137609
Item class	08A

**Description****Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant between - 20/+ 60°C. Maximum operating pressure 16 bar. Complies with ISO standard B.

**Note:**

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

**Technical description**

maximum operating pressure	10 bar
Connection plug nipple	1/4 in
usable hose length	8 m
Hose external Ø	12 mm
Connection quick-release coupling	1/4 in
Colour	blue
Material	PU spiral hose
Hose internal Ø	8 mm
maximum bursting pressure	35 bar

Type of product	Hose
-----------------	------

**Accessories**

Safety couplingExternal thread Connection external thread 1/4 in	080276 1/4
Coupling adaptor with external threadSet of 5 Connection external thread 1/4 in	080300 1/4