



## High Vis PU hose set with eSafe steel safety coupling Ø 11 × 16 mm, usable hose length: 10m



### Order data

Order number	080247 10
GTIN	7391390442239
Item class	08A

### Description

#### Version:

Very light, flexible, and abrasion-resistant PU hose with good retracting force.

Hose kit in the signal colour green (high-visibility).

#### Supplied with:

Includes steel **safety** quick-change coupling and steel coupling adaptor.

### Technical description

Hose internal Ø	11 mm
Hose external Ø	16 mm
Colour	green
maximum operating pressure	16 bar
Connection plug nipple	1/4 in
usable hose length	10 m
Type of product	Hose

---

## Accessories

Safety shut-offExternal thread Connection external thread  
1/2 in

080285 1/2

Coupling adaptor with external thread5-piece set  
Connection external thread 1/2 in

080290 1/2