

Garant**Dead-blow hammer with nylon inserts Hickory handle, Hammer head Ø: 32mm****Order data**

Order number	754750 32
GTIN	4045197923547
Item class	71D

Description**Version:**

Strong steel central piece (T-piece) with spigot and collar for holding the inserts. Inserts of wear-resistant nylon (medium hard). **Dead-blow** due to additional weights in the hammer body. Upon impact, the weights are thrown downwards and inhibit rebounding.

With handle of American hickory wood.

Application:

For straightening or aligning components on machine tables or for application of light impacts in assembly work.

Spare part:

For spare inserts see No. 754720 and 754730.

See No. 754840 for spare blade.

Technical description

Handle length	285 mm
Hammer head Ø	32 mm
Overall length	320 mm
Weight	0.391 kg
Head length with inserts	100 mm
Type of product	Hammer

Accessories

Spare insert, nylonflat Hammer head Ø 32 mm	754720 32
Spare insert, nylonconvex Hammer head Ø 32 mm	754730 32
Hickory hammer handle with wedge for head Ø 32 mm	754840 32