

### Support leg with power, Height 800 mm, Type: FR



#### Order data

Order number	927062 FR
GTIN	4062406755539
Item class	9GG

#### Description

**Version:**

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

**Supplied with:**

Support leg with two Schuko sockets with fastening materials, not wired.

**Colour:**

RAL 7035 light grey **powder-coated.**

**Note:**

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop.

Pre-assembled workbenches must be secured against tipping.

#### Technical description

Height	800 mm
Width	50 mm
Power supply	Mains-powered

## Data sheet

Rated current	16 A
Depth	700 mm
Socket type	E
suitable for worktop depth	750 mm
Nominal voltage	250 V
Design version	Steel hollow section construction
Material thickness	1 mm
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Product name attribute	Height 800 mm
Type of product	Power module

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/927062-FR>