Data sheet

Cordless drill / driver, Type: M12BDD2

Order data

Order number	070210 M12BDD2
GTIN	4002395002627
Item class	03L

Description

Version:
MILWAUKEE – Cordless drill / driver Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display.** Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **With low-maintenance 4-pole DC motor with high torque.**
- **REDLINK™ electronics – reliable load management with overload protection for long working life of the battery, motor and gearbox.**
- **Only 185 mm overall.**
- **19-step torque limit adjustment, plus drill steps.**

Advantage:
Very compact, only 185 mm overall length.
Supplied with:
Supplied with 2× 12 V / 2.0 Ah Li-ion batteries, charger, belt clip, HD box.
Note:
See No. 073814, No. 073815, No. 073829 and No. 073840 for suitable replacement batteries and chargers.

Technical description

maximum twist drill size ∅ in wood	22 mm
typical application	Medium
maximum speed 1st speed	0 - 400 min^{-1}
Motor design	4-pole motor
maximum torque hard	30 Nm
Battery capacity	2 Ah
Weight	1.2 kg
Quick-clamping chuck range	1.5 - 10 mm
maximum speed 2nd speed	1500 min^{-1}
maximum vibration to EN	< 2.5 m/s^2
Manufacturer's designation	M12BDD-202C
maximum twist drill size ∅ in steel	10 mm
Battery voltage	12 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	Modular case (HD=Heavy Duty)
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Suitable for material	wood
Suitable for material	Wood
Type of product	Drill/driver

Suitable products

https://www.hoffmann-group.com/GB/en/hom/p/070210-M12BDD2