

Garant**Value pack CNMG indexable insert finishing 30 pieces HB7020-2****Order data**

Order number	GG2401 120408
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.8 mm
Contents	250060 HB7010-2
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \max}$	4.25 mm
ISO code indexable insert	CNMG 120408
Cutting depth $a_{p \min}$	0.55 mm
Main application	P
Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	170 - 500 mm/min

Data sheet

Tool material	Carbide
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2401 120408