

**WNMG indexable insert for medium machining 50 pieces, HBT130, Size: 080404****Order data**

Order number	GG3985 080404
GTIN	4067263095040
Item class	GGN

Technical description

Coating	TiCN
Number of changes/inserts	6
Corner radius	0.4 mm
Tool material	Carbide
Cutting depth a_p	0.5 - 5 mm
Main application	M
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2.75 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	50 - 200 mm/min

Data sheet

ISO code indexable insert	WNMG 080404
Quantity	50
Feed f	0.12 - 0.45 mm/rev.
Contents	252094 HBT130
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3985 080404