

**VCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 160402****Order data**

Order number	GG3565 160402
GTIN	4067263092278
Item class	GGN

Technical description

Tolerance	M
Main application	M
Tool material	Carbide
Cutting speed v_c main application	80 - 270 mm/min
Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_{p \text{ min}}$	0.15 mm
ISO code indexable insert	VCMT 160402
Cutting depth $a_{p \text{ max}}$	2.5 mm
Number of changes/inserts	2
Contents	261370 HB7130-2
Finishing/roughing assignment	Finishing

Data sheet

Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.2 mm
Quantity	30
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3565 160402