


SCMT indexable insert for finishing 50 pieces, HB7010-2, Size: 09T304

Order data

Order number	GG2830 09T304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.4 mm
ISO code indexable insert	SCMT 09T304
Tool material	Carbide
Main application	P
Cutting speed v_c main application	150 - 500 mm/min
Quantity	50
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	4

Data sheet

Cutting depth $a_{p \max}$	3.25 mm
Contents	260742 HB7010-2
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2830 09T304