

Garant**KNUX indexable insert for medium machining 50 pieces, HB7020-2, Size: 160405R****Order data**

Order number	GG2439 160405R
GTIN	4067263094562
Item class	GGN

Technical description

Main application	P
Cutting depth a_p	0.3 - 4 mm
Cutting speed v_c main application	130 - 370 mm/min
Contents	251030 HB7020-2
Tool material	Carbide
Cutting depth $a_{p \min}$	0.35 mm
Cutting depth $a_{p \max}$	4 mm
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	2
Finishing/roughing assignment	Finishing

Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2439 160405R