


Garant**Value pack GARANT Master Steel solid carbide mini milling cutter HPC, 5 pieces****Order data**

Order number	GG2291 12
GTIN	4067263091790
Item class	GGN

Description**Version:**

Extra short cutter for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

Save the regrinding costs: It is cheaper to use a carbide mini milling cutter to the limit of wear and throw it away, than to regrind it.

Same as No. 202291.

Technical description

Flute length L_c	16 mm
Overall length L	73 mm
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.07 mm
Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.06 mm
Shank $\varnothing D_s$	12 mm
Direction of infeed	horizontal, oblique and vertical

Corner chamfer angle	90 degrees
Cutting edge Ø D _c	12 mm
Helix angle	30 degrees
No. of teeth Z	3
Tolerance nominal Ø	e8
Contents	5
Shank form	HB
Shank	DIN 6535 HB to h6
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Works standard
Type	N
Cutting width a _e for milling operation	0.3×D for side milling
Cutting width a _e for milling operation	0.5×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	120 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P

Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	85 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Accessories

GARANT Master Steel solid carbide mini milling cutterHPC
Ø e8 DC 12 mm

202289 12

GARANT Master Steel solid carbide mini-milling cutterHPC
Ø e8 DC 12 mm

202291 12