

**CCMT indexable insert for finishing 50 pieces, HB7020-2, Size: 09T308****Order data**

Order number	GG2805 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.8 mm
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	140 - 400 mm/min
ISO code indexable insert	CCMT 09T308
Cutting depth $a_{p \max}$	3.25 mm
Main application	P
Contents	260060 HB7020-2
Number of changes/inserts	2

Data sheet

Tool material	Carbide
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2805 09T308