

Garant**Value pack DNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2425 110404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DNMG 150608
Cutting depth $a_{p \min}$	0.25 mm
Main application	P
Cutting depth a_p	0.3 - 4 mm
Number of changes/inserts	4
Cutting speed v_c main application	140 - 440 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Contents	250752 HB7010-2
Feed f	0.2 - 0.5 mm/rev.
Corner radius	0.4 mm
Tool material	Carbide

Data sheet

Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2425 110404