



Value pack DNMG indexable insert roughing 30 pieces HBT020

Order data

Order number	GG3910 150608
GTIN	4067263093039
Item class	GGN

Technical description

Feed f	0.2 - 0.6 mm/rev.
Main application	P
Cutting speed v_c main application	80 - 260 mm/min
Finishing/roughing assignment	Roughing
ISO code indexable insert	DNMG 150608
Tool material	Carbide
Cutting depth a_p	1.8 - 6 mm
Cutting depth $a_{p \max}$	3.75 mm
Contents	250786 HBT020
Corner radius	0.8 mm
Number of changes/inserts	4
Coating	TiCN
Cutting depth $a_{p \min}$	0.55 mm
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PR
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3910 150608
