

**Garant****TCMT indexable insert for finishing 50 pieces, HB7130-2, Size: 16T308****Order data**

|              |               |
|--------------|---------------|
| Order number | GG3544 16T308 |
| GTIN         | 4067263092278 |
| Item class   | GGN           |

**Technical description**

|                                      |                   |
|--------------------------------------|-------------------|
| Contents                             | 260958 HB7130-2   |
| Quantity                             | 50                |
| Tool material                        | Carbide           |
| Cutting depth $a_{p \min}$           | 0.55 mm           |
| Cutting speed $v_c$ main application | 80 - 270 mm/min   |
| ISO code indexable insert            | TCMT 16T308       |
| Finishing/roughing assignment        | Finishing         |
| Cutting depth $a_{p \max}$           | 4 mm              |
| Number of changes/inserts            | 3                 |
| Feed $f$                             | 0.1 - 0.3 mm/rev. |
| Corner radius                        | 0.8 mm            |

## Data sheet

|                     |                              |
|---------------------|------------------------------|
| Coating             | coated                       |
| Cutting depth $a_p$ | 0.2 - 1.5 mm                 |
| Main application    | M                            |
| Type                | HB7130-2                     |
| Cutting conditions  | slightly interrupted         |
| Chip breaker        | VS                           |
| Type of product     | Indexable insert for turning |

### Suitable products

No Shop URL available for: GG3544 16T308