

**DCGT indexable insert for finishing 50 pieces, HU7315-1, Size: 11T308****Order data**

Order number	GG3812 11T308
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.03 - 0.1 mm/rev.
Coating	uncoated
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.05 - 0.6 mm
Cutting depth $a_{p \min}$	0.05 mm
Cutting speed v_c main application	120 - 600 mm/min
ISO code indexable insert	DCGT 11T308
Tool material	Carbide
Quantity	50
Contents	260361 HU7315-1
Number of changes/inserts	2
Cutting depth $a_{p \max}$	0.2 mm
Corner radius	0.8 mm
Main application	N
Tolerance	G
Type	HU7315-1
Cutting conditions	continuous
Chip breaker	AF

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3812 11T308
