

Garant
Master Eco clamping toolholder short SVHCL 107.5°, for indexable inserts SV.., left

Order data

Order number	261299 16/11
GTIN	4069515004572
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
Insert size	11 mm
Functional width L ₄	20 mm
ISO code toolholder	SVHCR/L 1616X11
Overall length L	85 mm
suitable indexable insert	VC.. 1103..

Data sheet

Standard	Works standard
Shank size	16 mm
Set of insert screws	269023 1
Head length L ₁	35 mm
Application type	left-hand
Through-coolant	yes
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

No Shop URL available for: 261299 16/11