


Garant
GARANT Master Alu SlotMachine solid carbide roughing end mill HPC, DLC, Ø e8 DC: 6mm

Order data

Order number	205250 6
GTIN	4062406122218
Item class	11X

Description
Version:

For roughing.

Special profile for machining non-ferrous metals.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Ramping capability up to 45° .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

Note:

For **HB shanks** use order **no. 205251**.

Technical description

Overall length L	57 mm
Tolerance nominal Ø	e8
Cutting edge Ø D_c	6 mm
Overhang length L_1 incl. recess	19 mm
Feed f_z for slot milling in short-chipping aluminium	0.08 mm
Helix angle	35 degrees
Recess Ø D_1	5.5 mm
Flute length L_c	13 mm

Balance quality with shank	G 2.5 with HA
Shank Ø D _s	6 mm
Feed f _z for side milling in short-chipping aluminium	0.1 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
No. of teeth Z	3
Corner rounding r _v	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a _e for milling operation	0.4×D for side milling
Cutting width a _e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N
PA 66	suitable only under restricted conditions	120 m/min	N

PEEK	suitable only under restricted conditions	100 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		
Services			

Shank grinding Type HB	129100 HB
------------------------	-----------