

**CCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 060202****Order data**

Order number	GG2800 060202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.15 mm
Cutting depth a_p	0.2 - 1.5 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 500 mm/min
Contents	260050 HB7010-2
Cutting depth $a_{p \max}$	2 mm
Number of changes/inserts	2
Main application	P
Tool material	Carbide
Feed f	0.07 - 0.25 mm/rev.
Corner radius	0.2 mm

ISO code indexable insert	CCMT 060202
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2800 060202