

**CNMG indexable insert for roughing 30 pieces, HB7120-1, Size: 120416****Order data**

Order number	GG2912 120416
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	4
ISO code indexable insert	CNMG 160608
Corner radius	0.8 mm
Main application	M
Cutting depth a_p	1.5 - 6 mm
Tool material	Carbide
Feed f	0.25 - 0.6 mm/rev.
Cutting depth $a_{p \max}$	5.5 mm
Finishing/roughing assignment	Roughing
Contents	250328 HB7120-1
Cutting speed v_c main application	70 - 240 mm/min
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2912 120416
