


Master Mute boring bar A.. SVJCL 142°, for indexable inserts VC.., left

Order data

Order number	265039 12/07
GTIN	4069515036269
Item class	29E

Description
Version:

Carbide-reinforced round shank without clamping face.

Note:

Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Setting angle κ	142 degrees
Shank $\varnothing D_s$	12 mm
Overhang L_1	132 mm
Minimum pre-drill $\varnothing D_{min}$	14 mm
suitable indexable insert	VC.. 0702..
Centre offset L_3	7 mm
ISO code toolholder	A12X SVJCR/L07
Insert size	7 mm
Set of insert screws	269028 53
Series	Master Mute
Overall length L	189 mm
Standard	Works standard
Application type	left-hand
Shank type	Steel

Data sheet

Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265039-12/07>