

**DNMG indexable insert for medium machining 30 pieces, HBT130, Size: 150608****Order data**

Order number	GG3966 150608
GTIN	4067263094432
Item class	GGN

Technical description

Corner radius	0.8 mm
Finishing/roughing assignment	Roughing
Cutting depth $a_{p \max}$	3.75 mm
Number of changes/inserts	4
Tool material	Carbide
Feed f	0.15 - 0.55 mm/rev.
ISO code indexable insert	DNMG 150608
Cutting depth a_p	2 - 6 mm
Main application	M
Cutting speed v_c main application	40 - 180 mm/min

Data sheet

Coating	TiCN
Contents	250786 HBT130
Cutting depth $a_{p \min}$	0.55 mm
Quantity	30
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MR
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3966 150608