

**DCGT indexable insert for finishing 30 pieces, HU7315-1, Size: 11T302****Order data**

Order number	GG3808 11T302
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting depth $a_{p \max}$	2.75 mm
Contents	260356 HU7315-1
Corner radius	0.2 mm
Cutting speed v_c main application	120 - 600 mm/min
Tool material	Carbide
Cutting depth a_p	0.05 - 0.6 mm
Coating	uncoated
ISO code indexable insert	DCGT 11T302
Feed f	0.03 - 0.1 mm/rev.
Cutting depth $a_{p \min}$	0.15 mm
Main application	N
Quantity	30
Tolerance	G
Type	HU7315-1
Cutting conditions	continuous
Chip breaker	AF

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3808 11T302
