

Garant**TCMT indexable insert for medium machining 30 pieces, HB7035-2, Size: 110202****Order data**

Order number	GG2847 110202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	3
ISO code indexable insert	TCMT 110202
Contents	260980 HB7035-2
Cutting speed v_c main application	80 - 290 mm/min
Finishing/roughing assignment	Finishing
Main application	P
Corner radius	0.2 mm
Tool material	Carbide
Cutting depth $a_{p \min}$	0.15 mm

Data sheet

Cutting depth $a_{p \max}$	2.75 mm
Feed f	0.08 - 0.3 mm/rev.
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2847 110202