

**DCGT indexable insert for finishing 50 pieces, HU7315-1, Size: 070202****Order data**

Order number	GG3812 070202
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DCGT 070202
Cutting depth a_p	0.05 - 0.6 mm
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting speed v_c main application	120 - 600 mm/min
Contents	260351 HU7315-1
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Quantity	50
Main application	N
Feed f	0.03 - 0.1 mm/rev.
Coating	uncoated
Cutting depth $a_{p \min}$	0.15 mm
Tolerance	G
Type	HU7315-1
Cutting conditions	continuous
Chip breaker	AF

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3812 070202
