

**Garant****Value pack joint connection 6GP60****Order data**

Order number	GG8071 50
GTIN	4067263137320
Item class	GGN

**Description****Version:**

When using joining as a production technique, two or more components are connected through positive contact. When using the adhesive, the full jointing face is used to establish a solid connection. It allows for high force transfer and dynamic loads (high shear strength).

Type **6GP60**. For repair of worn areas and restoring correct fits. Large gap size suitable. Cured product can be machined by drilling, milling or grinding.

**Feature:**

Contents: 3 pieces

**Note:**

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

**Technical description**

Sustainability	GARANT GreenPlus
Storage temperature	5 - 23 °C
Suitable for material	Metal
Suitable for application area	Repairs

Suitable for application area	Joint connection
Maximum gap size	0.3 mm
Shape	paste
Operating temperature range	-55 - 180 °C
Flashpoint	100 °C
minimum break-away torque	18 Nm
Characteristics	mechanically resilient
Characteristics	fluorescent under UV light
Dynamic viscosity	200000 - 600000 mPas
Chemical basis	Methacrylate
Strength class	high-strength
Capacity	50 ml
Working life after date of manufacture	24 mo
Touch dry after	5 - 15 min
for thread size M to	M20
Functional strength to	3 - 6 h
Colour	silver
Series	GreenPlus
Density	1.13 g/cm <sup>3</sup>
Type of product	Jointing product

## Accessories

GARANT GreenPlus joint connection agent6GP60 Contents  
50 ml

088071 50