

**Garant****DCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 070202****Order data**

|              |               |
|--------------|---------------|
| Order number | GG3521 070202 |
| GTIN         | 4067263096337 |
| Item class   | GGN           |

**Technical description**

|                                      |                 |
|--------------------------------------|-----------------|
| Contents                             | 260449 HB7130-2 |
| ISO code indexable insert            | DCMT 070202     |
| Tolerance                            | M               |
| Main application                     | M               |
| Corner radius                        | 0.2 mm          |
| Cutting depth $a_p$                  | 0.5 - 2.5 mm    |
| Coating                              | coated          |
| Cutting depth $a_{p \max}$           | 1.75 mm         |
| Cutting speed $v_c$ main application | 70 - 240 mm/min |
| Cutting depth $a_{p \min}$           | 0.15 mm         |

## Data sheet

|                               |                              |
|-------------------------------|------------------------------|
| Tool material                 | Carbide                      |
| Number of changes/inserts     | 2                            |
| Finishing/roughing assignment | Finishing                    |
| Feed f                        | 0.1 - 0.4 mm/rev.            |
| Quantity                      | 30                           |
| Type                          | HB7130-2                     |
| Cutting conditions            | slightly interrupted         |
| Chip breaker                  | VM                           |
| Type of product               | Indexable insert for turning |

### Suitable products

No Shop URL available for: GG3521 070202