

**TCMT indexable insert for medium machining 30 pieces, HB7035-2, Size: 110204****Order data**

Order number	GG2847 110204
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	3
Cutting depth $a_{p \max}$	2.75 mm
Main application	P
ISO code indexable insert	TCMT 110204
Cutting speed v_c main application	80 - 290 mm/min
Feed f	0.08 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Contents	260982 HB7035-2
Cutting depth $a_{p \min}$	0.25 mm

Data sheet

Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2847 110204