

**CNMG indexable insert for medium machining 50 pieces, HB7120-1, Size: 120416****Order data**

Order number	GG2909 120416
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	1.05 mm
Corner radius	1.6 mm
Cutting speed v_c main application	80 - 260 mm/min
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Cutting depth $a_{p \max}$	4:25 mm
Quantity	50
Contents	250162 HB7120-1
Tolerance	M
Number of changes/inserts	4
Cutting depth a_p	0.5 - 4 mm
Tool material	Carbide
ISO code indexable insert	CNMG 120416
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2909 120416
