

**TCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 16T308****Order data**

Order number	GG3541 16T308
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \min}$	0.55 mm
Contents	260958 HB7130-2
Cutting speed v_c main application	80 - 270 mm/min
Main application	M
Cutting depth $a_{p \max}$	4 mm
Coating	coated
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Corner radius	0.8 mm

Data sheet

Feed f	0.1 - 0.3 mm/rev.
Tool material	Carbide
Quantity	30
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3541 16T308