

**CNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 09T308****Order data**

Order number	GG2902 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Main application	M
Feed f	0.15 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	4
Corner radius	0.8 mm
Tool material	Carbide
Contents	250052 HB7140-2
Finishing/roughing assignment	Finishing
ISO code indexable insert	CNMG 09T308
Coating	coated
Cutting speed v_c main application	70 - 230 mm/min

Data sheet

Cutting depth a_p	0.3 - 2.5 mm
Cutting depth $a_{p \max}$	3:25 mm
Quantity	30
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2902 09T308