

**TCMT indexable insert for finishing 30 pieces, HB7020-2, Size: 16T304****Order data**

Order number	GG2840 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4 mm
Cutting speed v_c main application	140 - 400 mm/min
Contents	260956 HB7020-2
Corner radius	0.4 mm
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	3
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	TCMT 16T304
Finishing/roughing assignment	Finishing
Tool material	Carbide

Main application	P
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2840 16T304