

**CCMT indexable insert for finishing 50 pieces, HB7035-2, Size: 09T308****Order data**

Order number	GG2806 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	120 - 350 mm/min
Contents	260060 HB7035-2
ISO code indexable insert	CCMT 09T308
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \max}$	3.25 mm
Tool material	Carbide
Corner radius	0.8 mm
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	2
Finishing/roughing assignment	Finishing

Data sheet

Cutting depth $a_{p \min}$	0.55 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2806 09T308