

**TCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 16T304****Order data**

Order number	GG3543 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	90 - 290 mm/min
Number of changes/inserts	3
Quantity	50
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	4 mm
ISO code indexable insert	TCMT 16T304
Contents	260956 HB7120-1
Main application	M
Tool material	Carbide
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.3 mm/rev.
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3543 16T304
